

		Q' ty
Incorporated	Main unit SFM-1	1
	Base for semen flask	1
	Sealed straw receiver	1
	Anvil assembly	1
	Ultrasoung oscillator	1
Accessories	Suction needle (5pcs/set)	1
	Tube for suction needle, 25cm, 10pcs/set	1
	Injection needle(5pcs/set)	1
	Tube for injection needle, 65cm, 10pcs/set	1
	Weight (5pcs)	1
	Packing (100pcs)	1
	Straw tube for initial operation (500pcs)	1
	Power cable (For US oscillator)	1
	Power cable (For main unit)	1
	Hexagonal wrench set	1
	Operation manual	1
	Warranty certificate	1

Specifications

Model	SFM-1 for 0.5mL	SFM-1 for 0.25mL
Product code	01156500	01156600
Straw size	0.5mL	0.25mL
Dimensions (mm)	W400 × D560 × H380	
Weight	Approx. 40kg	
Power source	AC100V or AC220V (50Hz/60Hz)	
Power consumption	400W	

*Specifications are subject to change without prior notice.

15-7-2005


Distributor

Manufacturer

FHK Fujihira Industry Co., Ltd.
 6-11-6 Hongo Bunkyo-ku Tokyo
 113-0033 Japan
 Tel: +81-3-3812-2270 Fax: +81-3-3812-3663
 E-mail: overseas@fujihira.co.jp


Single Straw Filling and Sealing Machine

Single straw filling and sealing machine **SFM-1**




FHK
Fujihira Industry Co., Ltd.


Stable and reliable semen straw production with SFM-1.
2 operation mode selectable: Continuous operation
& production for designated number of straws



Straw hopper with capacity 650pcs (0.5ml straws)



Filling and sealing station



Touch panel screen



Filling pressure adjustable

